Shandong, China

\$4,800.00/sets 1-2 sets

km

1

box

1-7days

100sets

360D

1800W KM High Power Handle With 6 Exchangeable Spot Size For Permanent Hair Removal

Basic Information

- Place of Origin:
- Brand Name:
- Model Number:
- Minimum Order Quantity:
- Price:
- Packaging Details:
- Delivery Time:
- Supply Ability:

2 Years

STANDING

Other, Field Maintenance And Repair

Commissioning And Training

For Home Use, For Commercial

1064nm 3 Waves Titanium

6-16 Laser Bars Option

15 Inch Color Touch Screen

Service, Online Support, Free Spare Parts, Video Technical Support, Field Installation,

Acne Analysis, Pigmentation Analysis, Skin Wrinkle Analysis, Detect Skin Moisture

Laser Hair Removal System 755nm 808nm

12*20mm 15*27mm 12*35mm 14*14mm

808nm-810nm/808+755+1064nm Option

English, Spanish, Portuguese, Turkish...

After-sales Service
Provided:

Product Specification

• Type:

Warranty:

- Feature:
- Application:
- Name:
- Spot Size:
- Laser Wavelength:
- Laser Bars:
- Languages Option:
- Screen:



VEC professional

More Images



KM NEW LASER screen automatically recognizes the spot size Adjustable spot



Adjustable spot six different sizes in total



Our Product Introduction




Our Advantages




KM LASER Machine Upgrade points


- 1)360 plus uses 6D TIP technology.
- 2) Six different light spots are automatically recognized by the 6 in1 system on one handle
- 3)Automatically adjusted to the treatment parameters of the corresponding TIP,Avoid burns or lack of energy 4) **Double-row lasers,Energy utilization rate is over 95%**
- 5 With hair follicle analyzer that can see changes in hair follicles
- 6 Support wireless charging












When you change the spot size, the system automatically adjusts the parameters




Identify	Intelligent AI recognition technology (System automatically identifies the installed spot and automatically adjusts to the treatment parameters of the corresponding TIP)	No automatic recognition
Risk	Intelligently adjust parameters to avoid burns or insufficient energy	It is easy to get burned or lack of energy when adjusting the light spot
Light loss	Passed the American Tracepro optical experimental data test, the light energy transmittance is 96.5!!	Failed the light decay test
Transmission	Wireless transmission, no problem of poor contact	Wired transmission is prone to poor contact or no data transmission
Fixed way	Magnetic force + fixing pin + curved edge teeth, no light leakage and stronger	JUST Magnetic, The light source easily diverges, Easy to deform
Chip	USA Coherent imported laser bar WITH certification	NO certification
Energy utilization rate	Energy utilization rate is over 95%	Energy utilization rate is only 60%
Certification	MDSAP ,Medical CE , TGA, TUV	NO MDSAP,TGA
B 1.11 A		

Passed the American Tracepro optical experimental data test, the light energy transmittance is 96.5 %





Mobile phone wireless charging





Why choose KM diode laser hair removal machine?


*Much stable and higher powerful new golden welding laser module with USA Coherent imported laser bar WITH certification. It can shot about 500 million times

*Double water filters, only change filters per 6 months and 1 year. And some old filters in some machines need change filter every month. Save much maintainance cost and times for you .

*New Italy Bluid-o-tech imported water pump replaced Chinese pump with better cooling system and more quiet duirng treatment. Those obvious difference will be found when your customers compare with some machines with Chinese water pump.

*Japan TDK Six way power supply replaced four way power supply, much higher and stable output. *TEC cooling system, can control water temperature by yourself to keep 808 diode laser machine running continuously within 24 hours even in Summer. Same function as your A/C in your house .

*Various power laser modules for your option , 300W 500W 600W 800W 1000W 1200W 1600W ... (6bars 10basr 12bars 16bars) *Single 808 wave, 755nm/808nm/1064nm double wave and triple wave for option.



755+808+1064nm Platinum Style Technology.

The 3 waves works in the same handle at the same time: 755nm for white skin(fine, golden hair) 808nm for yellow/neutral skin 1064nm for black(black hair)





PERMANENT REDUCTION IN HAIR REGROWTH



Week 1-3



Week 4-5



Week 6-7



After Week 8

Laser type	Diode laser
Laser wavelength	808nm or 3 wave 755&808&1064nm
Spot size	12*12 mm2,12*20 mm2,15*27mm2, 12*35 (optional)
Pulse width	1-400 ms (adjustable), 300ms, 200ms(optional)
Energy	1-160 J/cm2 (adjustable) 280J 360J(optional)
Frequency	1-10 Hz(adjustable)
Language	English, Spanish, Italian, German, French, Turkish or any other language as requested
Skin type	I-VI skin type
Update system	USB update
Rent System	Optional
12 Display	12.4"/15inch color touch LCD display
Laser module power	600W/800W/1000w/1200W/1600W
Cooling	water + air + semiconductor + A/C+TEC big cooler part
Voltage	110V/220V±20V, 50/60Hz

<u>F*A Support for querying 510K-codes on the official website</u> KM LASER Since 2009, the leading manufacturer of aesthetic machines in the industry, focusing on high quality and high technology of equipment

Back To Search Results

New Search

Device Classification Name	powered laser surgical instrument
510(k) Number	K182924
Device Name	Diode Laser Treatment System
Applicant	Weifang KM Electronics Co., LTD No. 7999 Health East Street, High-Tech District Weifang, CN 261000
Applicant Contact	Andy Pang
Correspondent	Weifang KM Electronics Co., LTD No. 7999 Health East Street, High-Tech District Weifang, CN 261000
Correspondent Contact	Andy Pang
Regulation Number	878.4810
Classification Product Code	GEX
Date Received	10/19/2018
Decision Date	04/15/2019
Decision	Substantially Equivalent (SESE)
Regulation Medical Specialty	General & Plastic Surgery
510k Review Panel	General & Plastic Surgery
Summary	Summary
Туре	Traditional
Reviewed by Third Party	No
Combination Product	No

We have MDSAP AND TUV ISO 13485 .Certified by 27 EU countries, Brazil, New Zealand, Japan, Canada, and the United States


	Certificate Number CN20/123456809	<u> </u>
Weifang	KM Electronics Co., Ltd.	STATES THE STATE
No	.7999 Health East Street, High-tech District, Weifang City, Shandong, 261205, P.R. China	
has been audited atta	Dun & Bradstreet D-U-N-S identification number : 55-443-3424 inst the onteria stated below and found to contains to those onteria for the acope contained in this coefficient	
	MDSAP(ISO 13485:2016)	SGS
Therapeutic Goods (M	Australia edical Devices) Regulations: 2002, Schedule 3 Part 1 (excluding Part 1.6) – Full Quality Assurance Procedure (including design)	MDSAP
	Medical Devices Regulations – Part 1 SDR 90/262 21 CFR 820 / 21 CFR 805 / 21 CFR 806 / 21 CFR 807 – Subgarts A to D	
Design, Mar	sufacture and Distribution of Diode Laser Treatment System	
	This certificate is valid from Effective Date: 2020-12-09 until Expiry Date: 2023-12-08	
A	This certificate is valid from Effective Date: 2020-12-09 until Expiry Date: 2023-12-08 nd remains valid subject to satisfactory surveillance audits. Re certification audit due before 2023-09-11 Issue 1. Certified since 2020-12-09	
	Authorised by J Hall Business Managor	
	Jonathan M. Hall	
	SGS United Kingdom Ltd Rossmore Business Park, Ellesmene Part, Chashine, CH65 SERUK 1-44 (0151 305696 www.says.com SGS United Kingdom Ltd is an MCSAP authorised auditing organization	
	SGS United Kingdom LDI is all MUSAP authorited audoing organization SGS MDSAP 1116 Page 1 of 1	
	-3961001	
-		
SC \$	SSGSUS CAL	
-	nactos tra Conçuey, subject to 16 General General Constituent al	🕨 🕷 🖉 🛛
Cartification Stervice Riteration & drawn Nr Insues established for fig. News upp. sterv Ary unanification after artista document.	A accessible of asses representatives, and, anothers then be produced as Calcella deventations are only invested and areas. The adventish produced rates has welled and accessible adventation approaches and the developments'. Accessible and and approaches and the developments'.	
Controlation Strends Altondow o dawn Vi asswar entablished h 16g (Inves up) new Ary snachwidad daw al they document	A santability of a source sponsorbers, and a santability of source sponsorbers of the source sponsorbers of the source sponsorbers of source studies of the source sponsorbers of the source sponsorbers of source studies of the source sponsorbers of the source sponsorbers of source studies of the source sponsorbers of the source sponsorbers of source studies of the source sponsorbers of the source spon	
Controlanda Seniori Resolutivo di Seniori Seniori and Seniori Seniori and Seniori Seniori and Seniori Alexandro di	A statute of the s	
Cathlands Saint Hannis an Ganari Hiji Nanan spirat Hiji Nanan spirat An Shina Saint Hannis Hannis Saint Hannis Han	A statistic statis statistic statistic stat	
Cortificat		TÜVBheining
Certificat		TÜVRheinlan
Certificat Quality Manageme EN ISO 13485:201		TÜVRheinlan
	SX 2018364-1	TÜVRheinlan
Quality Manageme EN ISO 13485:201	SX 2018364-1	TÜVRheinlan
Quality Manageme EN ISO 13485:2010 Registration No.:	ent System S	TÜVRheinlan
Quality Manageme EN ISO 13485:2011 Registration No.: Organization:	s SX 2018384-1 Welfang KM Electronica Co., Ud No 7990, Heath East Street, High-tech Diatrict, Welfang City 201208 Shandong P.R. China	
Quality Manageme EN ISO 13485:2010 Registration No.:	s SX 2018364-1 Weiling KM Electronics Co., Ltd. No.7995, Health East Street. 201205 Shardong import Chy 201205 Shardong import Chy	
Quality Manageme EN ISO 13485:2011 Registration No.: Organization:	s SX 2018364-1 Welfang KM Electronics Co., Ltd. No.7909, Health East Street, High-tech District, Welfang City 201205 Shandong P.R. China Design and Development, Manufacture and	
Quality Manageme EN ISO 13485:2011 Registration No.: Organization:	s SX 2018364-1 Welfang KM Electronics Co., Ltd. No.7909, Health East Street, High-tech District, Welfang City 201205 Shandong P.R. China Design and Development, Manufacture and	Detribution of Diode Laser
Quality Manageme EN ISO 13485:2011 Registration No.: Organization:	s SX 2018364-1 Welfang KM Electronics Co., Ltd. No.7909, Health East Street, High-tech District, Welfang City 201205 Shandong P.R. China Design and Development, Manufacture and	
Quality Manageme EN ISO 13485:2011 Registration No.: Organization:	s SX 2018364-1 Welfang KM Electronics Co., Ltd. No.7909, Health East Street, High-tech District, Welfang City 201205 Shandong P.R. China Design and Development, Manufacture and	
Quality Manageme EN ISO 13485:2011 Registration No.: Organization:	s SX 2018364-1 Welfang KM Electronics Co., Ltd. No.7909, Health East Street, High-tech District, Welfang City 201205 Shandong P.R. China Design and Development, Manufacture and	
Quality Manageme EN ISO 13485:2011 Registration No.: Organization:	s SX 2018364-1 Welfang KM Electronics Co., Ltd. No.7909, Health East Street, High-tech District, Welfang City 201205 Shandong P.R. China Design and Development, Manufacture and	
Quality Manageme EN ISO 13485:2011 Registration No.: Organization:	s SX 2018364-1 Welfang KM Electronics Co., Ltd. No.7909, Health East Street, High-tech District, Welfang City 201205 Shandong P.R. China Design and Development, Manufacture and	
Quality Manageme EN ISO 13485:2011 Registration No.: Organization: Scope:	s SX 2018394-1 Weifang KM Electronica Co., Ltd No 7909, Hanite East Sreet High-tech Diatrict, Weifang City 201205 Shandong P.R. China Design and Development. Manufacture and Therapy Systems	I Distribution of Diode Laser
Quality Manageme EN ISO 13485:201 Registration No.: Organization: Scope:	s SX 2018364-1 Welfang KM Electronics Co., Ltd. No.7909, Health East Street, High-tech District, Welfang City 201205 Shandong P.R. China Design and Development, Manufacture and	
Quality Manageme EN ISO 13485:201 Registration No.: Organization: Scope: The Certification Bioly of management system Proof has Leen furthers as management system is an anagement system is an an an an a	s SX 2018394-1 SX 2018394-1 Wang WA Exectors Go. G. Ltd. High-bech Dairrick, Walfang Ort, 201205 Shanadong P.R. China Design and Development, Manufacture and Therapy Systems	I Distribution of Diode Laser
Quality Manageme EN ISO 13485:2010 Registration No.: Organization: Scope:	s X 2018384-1 S X 2018384-1 Wafang KM Electronics Co. Ltd. No 7909, Health East Street, High-lech Diatrict, Wafang City 201208 Shandong P.R. China Design and Development, Manufacture and Therapy Systems	I Distribution of Diode Laser

Machine Screen

OEM /ODM

- * 6 skin types

* Any language could be added * Logo could be added for free * 12.0 inch touch screen* With male and female , 6 skin styles to choose from ,easy to operate



DUST-FREE WORKSHOP



DUST-FREE WORKSHOP OF LASER MODULE ASSEMBLY FOR LONG SERVICE LIFE

Weifang KM Electronics Co., Ltd.14 years factory

2 years warranty

102 countries, 60000+ customers * 755+808+1064nm Ice Cooling Diode Laser Series, Multi-function series 2 in 1, 3 in 1, 6 in 1 series, Elight series, Q Switch ND YAG laser series, * Fat lossing : RF series ,Cavitation and so on.

Weifang KM Electronics Co., Ltd.is a professional factory focusing on development of beauty devices for 14 years. All the products are with

CE/ISO certification ,suitable for world market , mainly used on North America ,South America , Europe, our aim is on the development of beauty equipment, Pursuit of higher product quality, Making your business easier!


FACTORY FLOOR



5 PRODUCTION LINE FOR MACHINES ASSEMBLE AND HANDPEICE ASSEBLE



MACHINE DELIVERY



0, D3-H-17, D3-H-18, No. 7999, East Health Street, Yongchun Community, Qingchi Street, Hig Zone, Weifang, Shandong, China